

Axial expansion joint DN 185

Oper. pressure [bar]: 5

Oper. temp. range [K]: 90 ÷ 210

Oper. travel ranges (max.)
- axial [m] : -78 ÷ +110

Weight (max) [Kg] : 28.4

Spring rates (max.)
- axial [N/mm] : 100

Operating fluids : LO2

Bellows material : AISI 316 L

Application : A5 EPC RIE lines

Status : Qualified for flight

