

Gimbal expansion joint DN 60

Oper. pressure [bar]: 15
Oper. temp. range [K]: 20 ÷ 330
Oper. travel ranges (max.)
- angular [°] : ± 20
Weight (max) [Kg] : 6.5
Spring rates (max.)
- angular [N m/°] : 2
Operating fluids : LO2, LH2
Bellows material : AISI 316 L
Application : A5 EPC LBS lines
Status : Qualified for flight

